



Proceq 涂层和薄膜测试  
**Proceq ZWW 2100 - 2104**

湿膜测厚轮




**便于使用**

轻松 利用




**可靠性**

坚固 和 极其耐用的



**简单**

快 干净 向上



### 传感器 技术规格

ZWW 2100: 0  $\mu$ m - 25  $\mu$ m [0 mil - 0.98 mil]  
1  $\mu$ m (0.04 mil) 分辨率

ZWW 2101: 0  $\mu$ m - 50  $\mu$ m [0 mil - 1.97 mil]  
2  $\mu$ m (0.08 mil) 分辨率

#### 测量范围

ZWW 2102: 0  $\mu$ m - 125  $\mu$ m [0 mil - 4.92 mil]  
5  $\mu$ m (0.20 mil) 分辨率

ZWW 2103: 0  $\mu$ m - 250  $\mu$ m [0 mil - 9.84 mil]  
10  $\mu$ m (0.39 mil) 分辨率

ZWW 2104 : 0  $\mu$ m - 500  $\mu$ m [0 mil - 19.69 mil]  
20  $\mu$ m (0.79 mil) ) 解决

#### 重量

165 克 [0.36 磅]

Standards & Guidelines	Description
ASTM D1212	
ISO 2808	

---

SWISS  MADE



我们的业务遍及 100 多个国家，为世界各地的检验员和工程师提供最全面的 InspectionTech 解决方案，结合直观的软件和瑞士制造的传感器。  
[www.screeningeagle.com](http://www.screeningeagle.com)

请求报价



